

FleXbus IP55 Conductor Entry, Double Entry, 176 mm x 157 mm x 152 mm

Data Solutions

KATALOGNUMMER

FLEXCEIP55C1002



nVent ERIFLEX FleXbus IP55 Conductor Entries can be used for switchboard and/or power supply cover to upgrade an installation to IP55 level. Protect the nVent ERIFLEX FleXbus Conductor insulation against sharp edges from power supply or switchboard top cover.

SERTIFISERINGER



FUNKSJONER

I samsvar med RoHS

Made with soft PVC to follow any potential conductor bending radius

Sealing around the conductor is made by a self-fusing tape with a strong adhesive

Good resistance to solvent and hydrocarbon splashes

Adaptable to any nVent ERIFLEX FleXbus conductor cross section by cutting the top material with traditional cutter

High acid resistance

UV resistance

Flame retardant

PRODUKTEGENSKAPER

Artikkelnummer: 508143

Materiale: Polyvinylklorid

Kapslingsverdi: IP 55

Type: Dobbel inngang

Driftstemperatur: -40 to 140°C

A: 176mm

B.: 157mm

C.: 152mm

Lederstørrelse: 960 mm²; 1280 mm²; 1810 mm²

Dreiemoment (TQ): 2.5N·m

Enhetsvekt: 1kg

DIAGRAMMER



ADVARSEL

nVent-produkter må installeres og brukes bare som beskrevet i nVent sine instruksjonsark og opplæringsmateriell. Instruksjonsark er tilgjengelig på www.nvent.com og fra din nVent kundeservice-representant. Ukorrekt installasjon, misbruk, feilaktig anvendelse eller annen manglende etterlevelse av nVent sine instruksjoner og advarsler kan føre til produktfeil, skade på eiendom, alvorlige personskader og død og/eller gjøre garantien ugyldig.



Vår solide portefølje av merkevarer:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE