

## Syspend 180-Max flenskobling



Syspend 180-Max Flange Coupling attaches a tube to the enclosure, enabling 300-degree enclosure rotation and can be locked into a given position. The flange coupling has a safety stop and maintenance-free bearings.

### FUNKSJONER

---

Coupling can rotate 300 degrees with stop

Gasket, set screws, and mounting hardware are included

Assembled Syspend 180 HMI Arm System has a max weight load of 180 lb. (81.6 kg)

## SPESIFIKASJONER

---

**Materiale:** Aluminium  
**Overflate:** Pulverbelagt

Table 1/1

Katalognummer	E-nummer	Høyde	Bredde	Dybde	Farge	Fargekode
S1MFCG		101mm	125mm	100mm	Lys grå	RAL 7035
S1MFC	2411888	174mm	133mm	125mm	Kullsvart	RAL 9005

## ADVARSEL

---

nVent-produkter må installeres og brukes bare som beskrevet i nVent sine instruksjonsark og opplæringsmaterieill. Instruksjonsark er tilgjengelig på [www.nvent.com](http://www.nvent.com) og fra din nVent kundeservice-representant. Ukorrekt installasjon, misbruk, feilaktig anvendelse eller annen manglende etterlevelse av nVent sine instruksjoner og advarsler kan føre til produktfeil, skade på eiendom, alvorlige personskader og død og/eller gjøre garantien ugyldig.



Vår solide portefølje av merkevarer:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**