


FleXbus HCBC Clamp, 63 mm x 123 mm

Data Solutions

NÚMERO DE CATÁLOGO

FLEXCLAMP63



CERTIFICATIONS



CARACTERÍSTICAS

Rigid design assures even contact pressure

Installs quickly and easily

Ideal for on-site modifications

Made with non-magnetic material stainless steel for high-current connections to prevent the formation of magnetic fields

Contains crimped self-locking nut for vibration resistance and easy installation

No drilling needed to fix the FleXbus Conductor on the transformer/power supply palm

Includes voltage detection connecting point

RoHS compliant

CARATERÍSTICAS DO PRODUTO

Número do artigo: 508190

Material: Stainless Steel 304 (EN 1.4301)

A: 63mm

B: 123mm

C: 20mm

D: 43mm

Espessura (T): 4mm

Tamanho do orifício (HS): 5.5mm

Torque (TQ): 100N·m

Peso unitário: 0.53kg

Largura do condutor: 30 – 63mm

DETALHES ADICIONAIS DO PRODUTO

It is mandatory to use the HCBC Clamp associated with the HCBC Plate for proper Flexbus Conductor connection.

The minimum clearance distance is 14mm according to IEC 61439-1 with air pollution degree 3. If this distance cannot be respected, insulation material should be added between the metallic LV cover and the HCBC clamp. Flexbus IP2x Boots is also a solution.

If the Flexbus Conductors have a horizontal entry, an extender needs to be added between the power supply palm and HCBC Clamp and Plate.

DIAGRAMAS



AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.



O nosso forte portfólio de marcas:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE