

# Neutral Bar for TD Distribution Blocks, 125 A IEC

## Data Solutions

### NÚMERO DE CATÁLOGO

---

**NB-125A**



### CERTIFICATIONS

---



### CARACTERÍSTICAS

---

Attaches to four pole distribution blocks for increased wire capacity

Direct electrical connection

Strong mechanical assembly

Transparent protection cover

Halogen free

RoHS compliant

Conforms to EN 45545 obtaining an HL3 classification for chapter R23 and HL2 classification for chapter R22

### CARATERÍSTICAS DO PRODUTO

---

Número do artigo: 563841

Max Current Rating, IEC: 125A

Short Term Withstand Current (Icw) 1s: 4.5kA

Peak Short Circuit Current (Ipk): 30kA

Line Side Number of Connections: 3

Line Side Compact Stranded Wire Size: 10 - 25 mm<sup>2</sup>

Line Side Stranded Wire Size - Ferrule: 6 – 16mm<sup>2</sup>

Load Side Number of Connections: 9

Load Side Compact Stranded Wire Size: 2,5 - 6 mm<sup>2</sup>

Load Side Stranded Wire Size - Ferrule: 1,5 – 6 mm<sup>2</sup>

Profundidade (D): 37.4mm

Altura (H): 34.3mm

Largura (W): 142mm

Peso unitário: 0.17kg


Para uso com: TD-100-125AL (563830); TD-100-125ALL (563840)

Flammability Rating: UL® 94V-0

Em conformidade com: IEC® 60947-7-1

## DIAGRAMAS

---



## AVISO

---

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em [www.nVent.com](http://www.nVent.com) e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.



O nosso forte portfólio de marcas:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**