


Varistar CP Steel Door, Perforated With 1-Point Locking, Key Plate Only, RAL 7021, 38 U, 1800H 800W

Data Solutions

NÚMERO DE CATÁLOGO

21630-514



Varistar CP Perforated Steel Door, IP 20 with Single Point Locking.

CARACTERÍSTICAS

Perforated steel door with single point locking for IP 20 protection class

Opening angle 180°

Key lock cover

CARATERÍSTICAS DO PRODUTO

Rack Height: 38U

Altura: 1800mm

Largura: 800mm

Locking Type: Single Point Locking

Quantidade por embalagem: 1

Cor: Black Grey

Código de cor: RAL 7021

Em conformidade com: IEC 61587-1

Material: Aço

Família de produtos: Varistar CP

Product Type: Cabinet Door

Grau de proteção: IP20

Tipo: Steel Door, Perforated

Works With: Varistar CP

Net Weight: 16.878kg

DETALHES ADICIONAIS DO PRODUTO

24U - 33U IP20 doors have 2 hinges, 38U - 52U IP20 doors have 3 hinges to ensure robust IP20 closing structures for taller cabinets

Please order lever handle 24630003 and the DIN lock separately if you want to replace the 1333 DIN lock lever handle

Please purchase the grounding kit separately.

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.



O nosso forte portefólio de marcas:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE