

19" Cable Ducting

19" unit for easy and effective cable management (cable ducting).



CERTIFICATIONS



CARACTERISTICAS

19" Front panel for cable ducting

ESPECIFICAÇÕES

Accessory Type: Front panel
Product Type: Front Panel
Material: Aço

Table 1/3

Número de catálogo	Rack Height	Instalação	Quantidade por embalagem	Front Finish	Rear Finish	Código de cor
20118-734	1U	Screw-on Front	1	Painted	Painted	RAL 7035
20118-767	1U	Screw-on Front	1	Painted	Painted	RAL 7021
20118-736	2U	Screw-on Front	1	Painted	Painted	RAL 7035
20118-768	2U	Screw-on Front	1	Anodized	Conductive	RAL 7021

Table 2/3

Número de catálogo	Profundidade	EMC Shielding	Acabamento	Altura	Rack Width	Tipo
20118-734	1.5mm	Não	Pintura electrostática com Acabamento Texturado	43.6mm	95HP	19" Front Panel
20118-767	1.5mm	Não	Pintura electrostática com Acabamento Texturado	43.6mm	95HP	19" Front Panel
20118-736	1.5mm	Não	Pintura electrostática com Acabamento Texturado	88.1mm	95HP	19" Front Panel
20118-768	1.5mm	Não	Pintura electrostática com Acabamento Texturado	88.1mm	95HP	19" Front Panel

Table 3/3

Número de catálogo	Largura
20118-734	483mm
20118-767	483mm
20118-736	483mm
20118-768	483mm

DETALHES ADICIONAIS DO PRODUTO

Please order 19" assembly kit separately.

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

North America

All locations

+1.763.422.2661

Chat with us:

nvent.com/schroff

Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

nvent.com/schroff

Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

nvent.com/schroff



O nosso forte portefólio de marcas:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE