

# 19" Front Panel, Plastic



19" plastic made clip on Front Panels with esthetic design are specially made for the datacom vertical. The easy clip on panels help in air flow management and also simultaneously providing an appealing look for the network rack.

## CERTIFICATIONS



## CARACTERISTICAS

Attractive design

Simple fitting by clipping onto the 19" plane

## ESPECIFICAÇÕES

**Accessory Type:** Front panel

Table 1/3

| Número de catálogo | Tipo            | Instalação | EMC Shielding | Material | Front Finish | Rear Finish |
|--------------------|-----------------|------------|---------------|----------|--------------|-------------|
| 87927-991          | 19" Front Panel | Snapped in | Não           | ABS      | Raw          | Raw         |
| 87927-992          | 19" Front Panel | Snapped in | Não           | ABS      | Raw          | Raw         |
| 23130-623          | 19" Front Panel | Snapped in | Não           | ABS      |              |             |
| 23130-622          | 19" Front Panel | Snapped in | Não           | ABS      |              |             |

Table 2/3

| Número de catálogo | Código de cor | Rack Height | Altura | Rack Width | Largura | Profundidade |
|--------------------|---------------|-------------|--------|------------|---------|--------------|
|--------------------|---------------|-------------|--------|------------|---------|--------------|

|           |          |    |         |      |       |      |
|-----------|----------|----|---------|------|-------|------|
| 87927-991 | RAL 7035 | 1U | 43.71mm | 95HP | 482mm | 12mm |
| 87927-992 | RAL 7035 | 2U | 88.17mm | 95HP | 482mm | 12mm |
| 23130-623 | RAL 7035 | 6U | 266.6mm | 95HP | 483mm | 2mm  |
| 23130-622 | RAL 9005 | 6U | 266.6mm | 95HP | 483mm | 2mm  |

Table 3/3

| Número de catálogo | Quantidade por embalagem |
|--------------------|--------------------------|
| 87927-991          | 10                       |
| 87927-992          | 10                       |
| 23130-623          | 10                       |
| 23130-622          | 10                       |

## AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em [www.nVent.com](http://www.nVent.com) e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



O nosso forte portefólio de marcas:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**