

Panhead Screw, Torx, Self-Securing



Pan head Torx screws with different metric threads and lengths. With optional features like GND earthing function or "precoated thread".

Panhead Screw, Torx, St, zinc plated, M2.5 x 6 (Partially coated thread to prevent the screw from loosening on its own due to vibrations).

CERTIFICATIONS



CARACTERISTICAS

Pan Head Screw with torx, self-locking

ESPECIFICAÇÕES

Tipo:	Panhead Screw
Product Type:	Screw
Material:	Aço

Table 1/1

Número de catálogo	Length	Acabamento	Quantidade por embalagem	Tamanho da rosca	Works With
24560-159	6mm	Chapa de Aço Zincada	100	M2.5	Backplanes, Test Adapters
21500-039	9.3mm	Chapa de Aço Zincada	100	M2.5	Front Panels, Horizontal Rails, Type H, Horizontal Rails, Type R

DETALHES ADICIONAIS DO PRODUTO

Torque max. 0.2 Nm.

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



O nosso forte portfólio de marcas:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE