We connect and protect

Outdoor Modular 33 U 1730H 1900W 600D

Data Solutions

NÚMERO DE CATÁLOGO

10149-706

Telecom and Railway applications require sophisticated electronics in outdoor setups. nVent SCHROFF Outdoor cabinets shield such electronic components from extreme weather and vandalism, ensuring operational continuity. Modular contruction allows multiple configurations in size and function along with multiple cooling options.

CARACTERISTICAS

- Aluminium profile frame with removable, double-walled cladding
- IP 55 or NEMA 12~
- Double-walled
- Extensive range of 19" cabinet accessories
- Access to cabinet from front, all sides possible upon request
- 100 mm high plinth, 200 and 300 mm possible
- Top cover with louvers, can be upgraded with fans or A/C unit
- RAL 7035 powder coating, other colors available upon request

CARATERÍSTICAS DO PRODUTO

- Product Type: Outdoor Cabinet
- Família de produtos: Modular
- Rack Height: 33U
- Altura: 1730mm
- Largura: 1900mm
- Profundidade: 600mm
- Wall Type: Double Walled

Door Type: Plain; Triple Door

Burglar Resistance: Optional

Cooling: Passive

EMC Shielding: Optional

Frame Material: Aluminio

Battery Compartment: Optional

Acabamento: Pintura electrostática com Acabamento Texturado

Material: Aluminio; Aço

Mounting Setup: Optional

Quantidade por embalagem: 1

Plinth Height: 100mm

DETALHES ADICIONAIS DO PRODUTO

Height dimensions are without base/plinth.

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

O nosso forte portefólio de marcas:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.