We connect and protect

Outdoor Modular 38 U 1930H 900W 500D

Data Solutions

NÚMERO DE CATÁLOGO

10149-757

Telecom and Railway applications require sophisticated electronics in outdoor setups. nVent SCHROFF Outdoor cabinets shield such electronic components from extreme weather and vandalism, ensuring operational continuity. Modular contruction allows multiple configurations in size and function along with multiple cooling options.

CARACTERISTICAS

Aluminium profile frame with removable, double-walled cladding
IP 55 or NEMA 12~
Double-walled
Extensive range of 19" cabinet accessories
Access to cabinet from front, all sides possible upon request
100 mm high plinth, 200 and 300 mm possible
Top cover with louvers, can be upgraded with fans or A/C unit
RAL 7035 powder coating, other colors available upon request

CARATERÍSTICAS DO PRODUTO

Product Type: Outdoor Cabinet
Família de produtos: Modular
Rack Height: 38U
Altura: 1930mm
Largura: 900mm
Profundidade: 500mm
Wall Type: Double Walled

Door Type: Plain; Double Door

Cooling: Passive

EMC Shielding: Optional

Quantidade por embalagem: 1

Battery Compartment: Optional

Burglar Resistance: Optional

Acabamento: Pintura electrostática com Acabamento Texturado

Frame Material: Aluminio

Material: Aluminio; Aço

Plinth Height: 100mm

Mounting Setup: Optional

DETALHES ADICIONAIS DO PRODUTO

Height dimensions are without base/plinth.

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

O nosso forte portefólio de marcas:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.