

Varistar CP Glazed Door With 3-Point Locking, RAL 7021, 24 U, 1200 H, 800W

Data Solutions

NÚMERO DE CATÁLOGO

21630-417



Glazed door with 3 point locking allows stronger contact between door and the cabinet frame.

CARACTERÍSTICAS

Glazed Door With 3-Point Locking, With Lock

Lever handle with key insert (2 keys)

Opening angle 180°

Security glass, 6 mm

Standard fitting, lock on right-hand door

Can be retrofitted with lever handle 24630003 and DIN profile half cylinder with keys or push button

CARATERÍSTICAS DO PRODUTO

Rack Height: 24U

Altura: 1200mm

Largura: 800mm

Grau de proteção: IP20

Quantidade por embalagem: 1

Cor: Black Grey

Código de cor: RAL 7021

Em conformidade com: IEC 61587-1; IEC 61587-3

Acabamento: Pintura electrostática com Acabamento Texturado

Locking Type: 3-Point Locking

Material: Aço; Glass

Família de produtos: Varistar CP

Product Type: Cabinet Door

Tipo: Glass Door

Works With: Varistar CP

Net Weight: 17.196kg

DETALHES ADICIONAIS DO PRODUTO

24U - 33U IP20 doors have 2 hinges, 38U - 52U IP20 doors have 3 hinges to ensure robust IP20 closing structures for taller cabinets

Please order lever handle 24630003 and the DIN lock separately if you want to replace the 1333 DIN lock lever handle

Please purchase the grounding kit separately.

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.



O nosso forte portefólio de marcas:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE