

Monitor, Keyboard, Touchpad, 1 U Drawer, English Keyboard

Data Solutions

NÚMERO DE CATÁLOGO

60118-580



Designed for standard 19" rackmount designed for comfort
robust design for heavy use or harsh environment operation

CERTIFICATIONS



CARACTERÍSTICAS

Pull-out 17" TFT color monitor chassis, 1 U (resolution 1280 x 1024; connects to VGA interface)

Keyboard with different language keyboard layout (connects via USB)

Integral touchpad (connects via USB)

Voltage supply: Wide-range input (nominal mains voltage 110 to 240 VAC), Voltage supply 12, 24 and 48 VDC on request

Depth-adjustable mounting for different pitches of server panel/slide mounts; Mounting depth (dimension c = spacing of 19" profiles): dimension c 470 ... 740 mm

CARATERÍSTICAS DO PRODUTO

Rack Height: 1U

Quantidade por embalagem: 1

Cor: Jet Black

Código de cor: RAL 9005

Profundidade: 470mm

Product Type: Cabinet/Rack Drawer

Tipo: Monitor, Keyboard, Touchpad

Works With: 19" Cabinets

Keyboard Type: QWERTY UK

Net Weight: 15.2kg

DETALHES ADICIONAIS DO PRODUTO

Further versions on request. With trackball or numeric pad.

Other Keyboard layouts see user manual.

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.



O nosso forte portefólio de marcas:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE