

# eHandle



The security access control eHandle is an intelligent electromechanical locking system for server and networking cabinets. The eHandle seamlessly integrates with the network controller and Enlogic to serve as a hub for access control and environmental monitoring.

## CARACTERÍSTICAS

Security Access Control Handle for Enlogic's

Single or dual authentication

Triple embedded proximity card reader supporting MIFARE Classic 4k - UID, MIFARE Plus 2k - UID, MIFARE DESFire 4k - UID, HIS iClass - UID, HID 125 kHz prox - CSN and EM125 kHz Prox - CSN

Remote lock/unlock and remote monitoring

Local lock status indicator with multi-color LED indicator

Dual sided visible LED alarm beacons to indicate power, environmental, or security alarm status for the rack

User customizable key lock for manual over-ride

Embedded humidity sensor and additional environmental sensor port

Local data storage of 200 user credentials and 500 local events

Customizable alarm, LED status, and access configuration settings

## ESPECIFICAÇÕES

Table 1/1

| Número de catálogo | Product Type | Works With | Quantidade por embalagem | Plug Type | Removable Input Cable |
|--------------------|--------------|------------|--------------------------|-----------|-----------------------|
| EA9500             | Handle       | RackPower  | 1                        | RJ45      | Não                   |
| EA9502             | Handle       | RackPower  | 1                        | RJ45      | Não                   |

## AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em [www.nVent.com](http://www.nVent.com) e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)



O nosso forte portfólio de marcas:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**