

Heavy Duty Pipe Clamp per DIN 3567, Steel, Plain, 26.9mm OD, 3/4" Pipe, 20 DN

NUMĂR DE CATALOG

DIN027PL



CARACTERISTICI

For high static requirements in industrial construction

Suitable for fix point applications

Can be welded onto T-beam to form a sliding element

ATTRIBUTE PRODUS

Article Number: 400151

Material: Oțel

Finish: Plain

Outer Diameter (OD): 26.9 mm

Pipe Size: 3/4"

NB/DN: 20


Hole Size (HS): 11.5 mm

Width (W): 30 mm

Thickness (T): 5 mm

A: 64 mm

DIAGRAMS



AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Portofoliul nostru puternic de mărci:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE

