

# Heavy-Duty Pipe Clamp 349-365mm, 14" Pipe, DN 400, M20, Electrogalvanized

## NUMĂR DE CATALOG

### HDN350EG



## CARACTERISTICI

Fillet welded connector nut has flats to accommodate spanners

## ATTRIBUTE PRODUS

Article Number: 579067

Nut Included: Yes

Material: Oțel

Finish: Electrogalvanized

Outer Diameter (OD): 349 - 365 mm

Pipe Size: 14"

NB/DN: 350

Rod Size (RS): M20

Width (W): 50 mm

Thickness (T): 5 mm


Screw Diameter (Sc): 16 mm

Screw Diameter metric (Sc): M16

Screw Length (L): 60mm

Static Load: 12500N

## DIAGRAMS



## AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe [www.nvent.com](http://www.nvent.com) și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Portofoliul nostru puternic de mărci:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE

