

# nVent CADDY Macrofix Insulated M8/M10, 88–98 mm OD, 3" Pipe, 80 DN

## NUMĂR DE CATALOG

---

### MFD098



## CERTIFICATIONS

---



## CARACTERISTICI

---

Return-lip on the hanger prevents the rubber from detaching, eliminating rework during installation

Plastic washer prevents screws from falling out during installation

Combo head bolt works with slotted, hex, or Phillips drivers

Longer ears position the screw farther from the hanger, improving tool clearance when the screw is tightened

Combination nut can be attached to M8 or M10 threaded rod, simplifying material handling

Screw length has been optimized to accommodate an increased pipe range, reducing inventory

Category II noise reduction according to DIN EN ISO 3822-1

Compliant for sound insulation design according to DIN 4109

Reaction-to-fire classification is "E" in compliance with DIN EN 13501-1

## ATRIBUTE PRODUS

---

Article Number: 586012

Material: Oțel;EPDM-SBR Rubber

Finish: Electro galvanized

Temperature: -50 to 110 °C

Color: Black

Outer Diameter (OD): 88 - 98 mm

Pipe Size: 3"

NB/DN: 80

Rod Size (RS): M8;M10

Width (W): 23 mm

Thickness (T): 1.75 mm

Screw Diameter (Sc): 6

Screw Length (L): 37mm

Static Load: 2500N

## DETALII SUPLIMENTARE DESPRE PRODUS

Lining is EPDM rubber.

## DIAGRAMS



## AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe [www.nvent.com](http://www.nvent.com) și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

**North America**

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

**Europe**

Netherlands:

+31 800-0200135

France:

+33 800 901 793

**Europe**

Germany:

800 1890272

Other Countries:

+31 13 5835404

**APAC**

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Portofoliul nostru puternic de mărci:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**

