

# Flat Braided Power Shunt, 100 mm<sup>2</sup>, 250 mm

## Data Solutions

### NUMĂR DE CATALOG

---

**PBC100X250**



### CERTIFICATIONS

---



### CARACTERISTICI

---

Ideal for transformer-busduct link

Solid palms can be drilled to fit customer specific designs

Extra flexible power connection and good resistance to vibration

### ATTRIBUTE PRODUS

---

Article Number: 564000

Material: Copper

Finish: Tinned

Wire Diameter: 0.15mm

Cross Section: 100mm<sup>2</sup>

ΔT 30 K: 349A

$\Delta T$  50 K: 462A

Length (L): 250mm

A: 35mm

B: 40mm

C: 7mm


2 Bar Current Coefficient: 1.72

Unit Weight: 0.38kg

## DETALII SUPLIMENTARE DESPRE PRODUS

When used in parallel, the two shunts must be spaced with a minimum distance equal to the thickness of the shunt to allow air cooling.

## DIAGRAMS



## AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe [www.nvent.com](http://www.nvent.com) și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.



Portofoliul nostru puternic de mărci:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE