

Motion detector

Data Solutions

NUMĂR DE CATALOG

60130-067



Motion detector: Prepared for mounting on door box, detection method: movement, detection fields of radar are adjustable, wide field 4 m (W) x 2 m (D), narrow field 2 m (W) x 2.5 m (D), supply voltage 12 ... 24 VAC or 12 ... 30 VDC, power supply via connector on door plate.

CERTIFICATIONS



CARACTERISTICI

Supply voltage 12 ... 24 VAC or 12 ... 30 VDC, power supply via connector on door plate

Wide field 4 m (W) x 2 m (D)

Arrow field 2 m (W) x 2.5 m (D)

Detection method: movement

Prepared for mounting on door box

Detection fields of radar are adjustable

ATTRIBUTE PRODUS

Product Type: Sensor

Type: Motion Detector

Works With: Aisle Containment

Net Weight: 0.508kg

Package Quantity: 1

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.



Portofoliul nostru puternic de mărci:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE