

# nVent ERICO System 3000 Interceptor

## Data Solutions



### CARACTERISTICI

Dynamic response to the approach of a lightning downleader

Designed for lower height installations

Non-radioactive technology

No external power required

### SPECIFICAȚII

Table 1/2

| Număr de catalog | Article Number | Material                        | Temperature  | Installation Height (H) | Diameter 1 (Ø1) | Diameter 2 (Ø2) |
|------------------|----------------|---------------------------------|--------------|-------------------------|-----------------|-----------------|
| INTMKIVSS        | 702089         | Stainless Steel 316 (EN 1.4401) | -40 to 100°C | 20m max                 | 101.6mm         | 26.15mm         |

Table 2/2

| Număr de catalog | Article Number | Height (H) | Thread Size (TS) | Unit Weight |
|------------------|----------------|------------|------------------|-------------|
| INTMKIVSS        | 702089         | 348mm      | 1/2" BSPP        | 2.06kg      |

## DIAGRAMS

---



## AVERTIZARE

---

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe [www.nvent.com](http://www.nvent.com) și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.



Portofoliul nostru puternic de mărci:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**