

19" Drawer



19" Drawers allow mounting of laptops, writing surfaces for easy operations. The SCHROFF 19" drawer has a load capacity of 15 KG, allowing a wide range of products to be assembled into the drawer.

CERTIFICATIONS



CARACTERISTICI

Static load-carrying capacity 15 kg

Optional writing surface

SPECIFICAȚII

- Static Load:** 15kg
Product Type: Cabinet/Rack Drawer
Material: Oțel

Table 1/2

| Număr de catalog | Rack Height | Finish | Package Quantity | Color | Color Code | Front Finish |
|------------------|-------------|----------------|------------------|------------|------------|--------------|
| 20110-054 | 1U | Vopsit Pulbere | 1 | Light Grey | RAL 7035 | |
| 20110-061 | 1U | Vopsit Pulbere | 1 | | | Anodized |
| 20110-180 | 1U | Vopsit Pulbere | 1 | Black Grey | RAL 7021 | |
| 20110-056 | 3U | Vopsit Pulbere | 1 | Light Grey | RAL 7035 | |
| 20110-062 | 2U | Vopsit Pulbere | 1 | | | Anodized |

| Număr de catalog | Rack Height | Finish | Package Quantity | Color | Color Code | Front Finish |
|------------------|-------------|----------------|------------------|------------|------------|--------------|
| 20110-181 | 2U | Vopsit Pulbere | 1 | Black Grey | RAL 7021 | |
| 20110-063 | 3U | Vopsit Pulbere | 1 | | | Anodized |
| 20110-055 | 2U | Vopsit Pulbere | 1 | Light Grey | RAL 7035 | |
| 20110-182 | 3U | Vopsit Pulbere | 1 | Black Grey | RAL 7021 | |

Table 2/2

| Număr de catalog | Type | Works With |
|------------------|--------|--------------|
| 20110-054 | Drawer | 19" Cabinets |
| 20110-061 | Drawer | 19" Cabinets |
| 20110-180 | Drawer | 19" Cabinets |
| 20110-056 | Drawer | 19" Cabinets |
| 20110-062 | Drawer | 19" Cabinets |
| 20110-181 | Drawer | 19" Cabinets |
| 20110-063 | Drawer | 19" Cabinets |
| 20110-055 | Drawer | 19" Cabinets |
| 20110-182 | Drawer | 19" Cabinets |

DETALII SUPLIMENTARE DESPRE PRODUS

Please order 19" assembly kit separately.

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Portofoliul nostru puternic de mărci:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE