

AC Fan

Axial fan, 119 mm, with AC input. Replacement part for 1 U fan trays.



CERTIFICATIONS



CARACTERISTICI

119 mm DC fan with plug for connection cable

SPECIFICAȚII

Table 1/3

Număr de catalog	Works With	Width	Length	Height	Voltage AC	Frequency
20713-146	19" Fan Trays	119mm	119mm	25mm	115V	50/60 Hz
20713-142	19" Fan Trays	119mm	119mm	25mm	230V	50/60 Hz
20713-244	19" Fan Trays	119mm	119mm	38mm	115V	50/60 Hz
20713-147	19" Fan Trays	119mm	119mm	25mm	115V	50/60 Hz
20713-243	19" Fan Trays	119mm	119mm	38mm	230V	50/60 Hz
20700-001	19" Fan Trays	119mm	119mm	25mm	230V	50/60 Hz

Table 2/3

Număr de catalog	Airflow @ 50 Hz	Airflow @ 60 Hz	Noise Level @ 50 Hz	Noise Level @ 60 Hz	Power @ 50 Hz	Power @ 60 Hz
20713-146	84m³/h	90m³/h	29dB(A)	30dB(A)	8W	7W

Număr de catalog	Airflow @ 50Hz	Airflow @ 60Hz	Noise Level @ 50 Hz	Noise Level @ 60 Hz	Power @ 50 Hz	Power @ 60 Hz
20713-142	84m³/h	90m³/h	29dB(A)	30dB(A)	8W	7W
20713-244	162m³/h	192m³/h	37dB(A)	41dB(A)	15W	14W
20713-147	108m³/h	120m³/h	34dB(A)	38dB(A)	14W	11W
20713-243	162m³/h	192m³/h	37dB(A)	41dB(A)	15W	14W
20700-001	108m³/h	120m³/h	34dB(A)	38dB(A)	14W	11W

Table 3/3

Număr de catalog	Max Static Pressure	Ambient Temperature	Package Quantity
20713-146	23Pa	70°C	1
20713-142	23Pa	70°C	1
20713-244	73Pa	70°C	1
20713-147	41Pa	70°C	1
20713-243	73Pa	70°C	1
20700-001	41Pa	70°C	1

DETALII SUPLIMENTARE DESPRE PRODUS

Please order connection cable and protective grille separately.

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Portofoliul nostru puternic de mărci:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE