

CompacPRO Rear Panel With Vented Slots

The rear panel with vented slots can be used for the CompacPRO case. The rear panel is bolted on the rear frame.



CERTIFICATIONS



CARACTERISTICI

Al material 3.0 mm

SPECIFICAȚII

- Material:** Aluminiu
- Finish:** Anodized
- Works With:** Cases
- Product Family:** CompacPRO
- Type:** Rear Panel
- Product Type:** Side Panel

Table 1/1

Număr de catalog	Rack Height	Rack Width	Package Quantity
30823-027	3U	63HP	1
30823-033	4U	42HP	1
30823-036	4U	63HP	1
30823-021	3U	28HP	1
30823-024	3U	42HP	1

Număr de catalog	Rack Height	Rack Width	Package Quantity
30823-518	4U	84HP	1
30823-512	2U	84HP	1
30823-045	6U	63HP	1
30823-015	2U	42HP	1
30823-521	6U	84HP	1
30823-515	3U	84HP	1

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Portofoliul nostru puternic de mărci:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE