

Connection clamp with levers

Distribution Clamps for Distribution Box.



CARACTERISTICI

Connection clamp with levers

For all conductor types

3 or 5 conductors

Up to 4.00 mm²

SPECIFICAȚII

Table 1/2

Număr de catalog	Product Type	Color	Ambient Temperature	Clamp Quantity	Depth	Height
20118-902	Clamp	Transparent, Green	85°C max	3	18.8mm	8.4mm
20118-903	Clamp	Transparent, Green	85°C max	5	18.8mm	8.4mm

Table 2/2

Număr de catalog	Material	Max Current	Max Voltage	Package Quantity	Weight	Width
20118-902	Polycarbonate	20A	600V	10	2.5g	18.8mm
20118-903	Polycarbonate	20A	600V	10	4g	30mm

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și

avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Portofoliul nostru puternic de mărci:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE