


# DIN Rail

A DIN rail is a standard metal rail widely used for mounting circuit breakers and industrial control equipment inside equipment racks.



## CARACTERISTICI

Pre-Cut Lengths and with Perforations

Steel with electrogalvanized finishing

Comply with: EN 60715 Standards

## SPECIFICAȚII

**Product Type:** DIN Rail

Table 1/2

Număr de catalog	Material	Height	Length	Finish	Package Quantity	Depth
20118-879	Oțel	35mm	175mm	Oțel Zincat	4	7.5mm
20118-874	Oțel	35mm	275mm	Oțel Zincat	4	15mm
20118-872	Oțel	35mm	125mm	Oțel Zincat	4	15mm
20118-883	Oțel	35mm	575mm	Oțel Zincat	4	7.5mm
20118-875	Oțel	35mm	375mm	Oțel Zincat	4	15mm
20118-878	Oțel	35mm	125mm	Oțel Zincat	4	7.5mm
20118-880	Oțel	35mm	275mm	Oțel Zincat	4	7.5mm
20118-877	Oțel	35mm	575mm	Oțel Zincat	4	15mm
20118-882	Oțel	35mm	475mm	Oțel Zincat	4	7.5mm
20118-873	Oțel	35mm	175mm	Oțel Zincat	4	15mm
20118-881	Oțel	35mm	375mm	Oțel Zincat	4	7.5mm

Număr de catalog	Material	Height	Length	Finish	Package Quantity	Depth
20118-876	Oțel	35mm	475mm	Oțel Zincat	4	15mm
20118-893	Oțel	35mm	375mm	Oțel Zincat	10	7.5mm
20118-892	Oțel	35mm	275mm	Oțel Zincat	10	7.5mm
20118-891	Oțel	35mm	175mm	Oțel Zincat	10	7.5mm
20118-890	Oțel	35mm	125mm	Oțel Zincat	10	7.5mm
20118-895	Oțel	35mm	575mm	Oțel Zincat	10	7.5mm
20118-894	Oțel	35mm	475mm	Oțel Zincat	10	7.5mm
20118-889	Oțel	35mm	575mm	Oțel Zincat	10	15mm
20118-887	Oțel	35mm	375mm	Oțel Zincat	10	15mm
20118-885	Oțel	35mm	175mm	Oțel Zincat	10	15mm
20118-886	Oțel	35mm	275mm	Oțel Zincat	10	15mm
20118-884	Oțel	35mm	125mm	Oțel Zincat	10	15mm
20118-888	Oțel	35mm	475mm	Oțel Zincat	10	15mm

Table 2/2

Număr de catalog	Width
20118-879	175mm
20118-874	275mm
20118-872	125mm
20118-883	575mm
20118-875	375mm
20118-878	125mm
20118-880	275mm
20118-877	575mm
20118-882	475mm
20118-873	175mm
20118-881	375mm
20118-876	475mm
20118-893	375mm
20118-892	275mm
20118-891	175mm
20118-890	125mm
20118-895	575mm
20118-894	475mm
20118-889	575mm

Număr de catalog	Width
20118-887	375mm
20118-885	175mm
20118-886	275mm
20118-884	125mm
20118-888	475mm

## AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe [www.nvent.com](http://www.nvent.com) și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Portofoliul nostru puternic de mărci:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**