

AC Fan, 115 VAC, 119 x 119 x 25 mm, 108 m³h

NUMĂR DE CATALOG

20713-147

Axial fan, 119 mm, with AC input. Replacement part for 1 U fan trays.



CERTIFICATIONS



CARACTERISTICI

119 mm DC fan with plug for connection cable

ATRIBUTE PRODUS

Product Type: Fan

Works With: 19" Fan Trays

Width: 119mm

Length: 119mm

Height: 25mm

Voltage AC: 115V

Frequency: 50/60 Hz

Airflow @ 50 Hz: 108m³/h

Airflow @ 60 Hz: 120m³/h

Noise Level @ 50 Hz: 34dB(A)

Noise Level @ 60 Hz: 38dB(A)

Power @ 50 Hz: 14W

Power @ 60 Hz: 11W

Max Static Pressure: 41Pa

Ambient Temperature: 70°C

Gross Weight: 0.334kg

Package Quantity: 1

DETALII SUPLIMENTARE DESPRE PRODUS

Please order connection cable and protective grille separately.

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Portofoliul nostru puternic de mărci:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE