

Series 311 Short, Self-Compensation Inserter/Extractor

NUMĂR DE CATALOG

HS311-TC



The HS311 Series was designed in accordance with VITA 100 to provide up to 6:1 mechanical advantage for insertion and extraction of printed circuit boards with high density connector contacts. The integrated spring provides positive pressure on connectors during Card-Lok actuation and consistent self-compensation for board tolerances. The HS311-TC is ideal for 2nd level maintenance; can be operated with a gloved hand and no specialized tools are required.

⚠ WARNING: This product can expose you to chemicals including Chromium (hexavalent compounds), which is known to the State of California to cause cancer and reproductive health issue. For more information, go to www.P65Warnings.ca.gov.

CARACTERISTICI

Designed in accordance with VITA 100

Maintains positive pressure on connectors

Compliant with 2nd level maintenance; can be operated with a gloved hand, no specialized tools are required

Provides self-compensation for board tolerances

Integrated latching mechanism

Custom silkscreen available.

ATTRIBUTE PRODUS

Product Type: PCB Inserter/Extractor

Material: Aluminum Alloy 6061-T6

Finish: Hard Black Anodized

Design Feature: Tolerance Compensating

Package Quantity: 1

DETALII SUPLIMENTARE DESPRE PRODUS

From time to time, nVent may modify its product specifications to be in conformity with applicable industry, military or other relevant standards. Unless otherwise mutually agreed in writing, cancelled or superseded military specifications may be certified to the latest or superseding specifications. Products manufactured in conformity with such specifications will be deemed fully compliant whether or not you have been notified of such modifications, even if different from the original specification or those referenced by the customer.

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Portofoliul nostru puternic de mărci:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE