

Front Panel, Unshielded, Bottom Hinged

Unshielded front panel bottom hinged.



CERTIFICATIONS



CARACTERISTICI

Front panel can be unhinged at 135° (not RatiopacPRO) opening angle

Enables mounting on horizontal rails

SPECIFICAȚII

Depth (D):	2.5mm
Material:	Aluminiu
Finish:	Anodized
Accessory Type:	Front panel
Product Type:	Front Panel
Type:	Front Panel without Handle

Table 1/2

Număr de catalog	Rack Height	Rack Width	Package Quantity	Mounting	Front Finish	Rear Finish
20838-280	3U	28HP	1	Hinged, Bottom	Anodized	Conductive
20838-271	3U	42HP	1	Hinged, Bottom	Anodized	Conductive
20838-274	6U	42HP	1	Hinged, Bottom	Anodized	Conductive
20838-279	4U	84HP	1	Hinged, Bottom	Anodized	Conductive

Număr de catalog	Rack Height	Rack Width	Package Quantity	Mounting	Front Finish	Rear Finish
20838-272	3U	63HP	1	Hinged, Bottom	Anodized	Conductive
20838-275	6U	63HP	1	Hinged, Bottom	Anodized	Conductive
20838-278	4U	63HP	1	Hinged, Bottom	Anodized	Conductive
20838-277	4U	42HP	1	Hinged, Bottom	Anodized	Conductive
20838-276	6U	84HP	1	Hinged, Bottom	Anodized	Conductive
20838-273	3U	84HP	1	Hinged, Bottom	Anodized	Conductive


Table 2/2

Număr de catalog	Treated Edges	Complies With	EMC Shielding	Height (H)	Width (W)
20838-280	No	IEC 60297-3-101, IEEE 1101.1/10	No	128.4mm	141.9mm
20838-271	No	IEC 60297-3-101, IEEE 1101.1/10	No	128.4mm	213mm
20838-274	No	IEC 60297-3-101, IEEE 1101.1/10	No	261.8mm	213mm
20838-279	No	IEC 60297-3-101, IEEE 1101.1/10	No	172.9mm	426.4mm
20838-272	No	IEC 60297-3-101, IEEE 1101.1/10	No	128.4mm	319.7mm
20838-275	No	IEC 60297-3-101, IEEE 1101.1/10	No	261.8mm	319.7mm
20838-278	No	IEC 60297-3-101, IEEE 1101.1/10	No	172.9mm	319.7mm
20838-277	No	IEC 60297-3-101, IEEE 1101.1/10	No	172.9mm	213mm
20838-276	No	IEC 60297-3-101, IEEE 1101.1/10	No	261.8mm	426.4mm
20838-273	No	IEC 60297-3-101, IEEE 1101.1/10	No	128.4mm	426.4mm

DETALII SUPLIMENTARE DESPRE PRODUS

Front panel can be removed in opened position (> 135°).

DIAGRAMS



AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Portofoliul nostru puternic de mărci:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE