

Interscale Desktop Case, Non-Perforated

Flexible desktop case with integrated EMC protection. Based on the nVent SCHROFF Interscale platform and developed in accordance with IEC 60297-3-109.



CERTIFICATIONS



CARACTERISTICI

Modular desktop case consisting of 4 assembled parts

Developed according to IEC 60297-3-109 (under progress at IEC)

Integrated EMC protection

Ingress protection up to IP 30

Color RAL 7016

Modified or customized cases upon request

SPECIFICAȚII

Material:	Aluminiu; Oțel
Type:	Desktop
Product Family:	Interscale
Protection Rating:	IP30
Color Code:	RAL 7016
Product Type:	Small Form Factor Case

Table 1/2

Număr de catalog	Height	Package Quantity	Width	Depth	Cooling	Color
14820-133	43.7mm	1	132.6mm	132.6mm	Non-Perforated	Anthracite Grey
14820-297	88.1mm	1	399mm	310.35mm	Non-Perforated	Anthracite Grey
14820-255	88.1mm	1	221mm	221.45mm	Non-Perforated	Anthracite Grey
14820-295	88.1mm	1	399mm	221.45mm	Non-Perforated	Anthracite Grey
14820-154	43.7mm	1	221mm	177mm	Non-Perforated	Anthracite Grey
14820-375	132.6mm	1	310mm	221.45mm	Non-Perforated	Anthracite Grey
14820-254	88.1mm	1	221mm	177mm	Non-Perforated	Anthracite Grey
14820-155	43.7mm	1	221mm	221.45mm	Non-Perforated	Anthracite Grey
14820-395	132.6mm	1	399mm	221.45mm	Non-Perforated	Anthracite Grey
14820-134	43.7mm	1	133mm	177mm	Non-Perforated	Anthracite Grey
14820-195	43.7mm	1	399mm	221.45mm	Non-Perforated	Anthracite Grey
14820-175	43.7mm	1	310mm	221.45mm	Non-Perforated	Anthracite Grey
14820-275	88.1mm	1	310mm	221.45mm	Non-Perforated	Anthracite Grey
14820-397	132.6mm	1	399mm	310.35mm	Non-Perforated	Anthracite Grey
14820-197	43.7mm	1	399mm	310.35mm	Non-Perforated	Anthracite Grey

Table 2/2

Număr de catalog	Finish
14820-133	Aluminum-Zinc Plated, Vopsit Pulbere
14820-297	Aluminum-Zinc Plated, Vopsit Pulbere
14820-255	Aluminum-Zinc Plated, Vopsit Pulbere
14820-295	Aluminum-Zinc Plated, Vopsit Pulbere
14820-154	Aluminum-Zinc Plated, Vopsit Pulbere
14820-375	Aluminum-Zinc Plated, Vopsit Pulbere
14820-254	Aluminum-Zinc Plated, Vopsit Pulbere
14820-155	Aluminum-Zinc Plated, Vopsit Pulbere
14820-395	Aluminum-Zinc Plated, Vopsit Pulbere
14820-134	Aluminum-Zinc Plated, Vopsit Pulbere
14820-195	Aluminum-Zinc Plated, Vopsit Pulbere
14820-175	Aluminum-Zinc Plated, Vopsit Pulbere
14820-275	Aluminum-Zinc Plated, Vopsit Pulbere
14820-397	Aluminum-Zinc Plated, Vopsit Pulbere
14820-197	Aluminum-Zinc Plated, Vopsit Pulbere

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Portofoliul nostru puternic de mărci:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE