

Interscale for Mini-ITX, Conduction Cooled



Small form factor case with integrated EMC-shielding and conduction cooling for Mini-ITX boards, based on the innovative and flexible nVent SCHROFF Interscale platform.

CERTIFICATIONS



CARACTERISTICI

Modular case consisting of 3 easy to assemble parts; body, top cover and front panel

Cutout for Mini ITX I/O panel, power connector (Phoenix Contact, 0710028) and power switch (Schurter, MCS 18 Front)

Integrated EMC protection

Other dimensions, cutout shapes or locations, and screen printing available

Rigid construction requires only four screws

Board mounting studs installed

Color RAL 7016

SPECIFICAȚII

| | |
|---------------------------|------------------------|
| Height: | 94mm |
| Depth: | 189mm |
| Material: | Aluminiu |
| Type: | Desktop |
| Product Family: | Interscale |
| Protection Rating: | IP30 |
| Color Code: | RAL 7016 |
| Product Type: | Small Form Factor Case |

Table 1/1

| Număr de catalog | Design Feature | Package Quantity | Cooling | Color | Finish | Width |
|------------------|----------------|------------------|-------------------|-----------------|----------------|-------|
| 14830-005 | 10 mm Fins | 1 | Conduction Cooled | Anthracite Grey | Vopsit Pulbere | 184mm |
| 14830-006 | 20 mm Fins | 1 | Conduction Cooled | Anthracite Grey | Vopsit Pulbere | 184mm |

DETALII SUPLIMENTARE DESPRE PRODUS

Only the listed Interscale accessories are compatible.

Modified or customized cases up on request.

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Portofoliul nostru puternic de mărci:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE