

## Novastar Base/Plinth



Base Plate for Rear Cable Ducting which cut out for cable management. Opening is covered with plastic. Accessory brush strip can build in.

### CERTIFICATIONS



### CARACTERISTICI

Static load-carrying capacity 400 kg

Adjustable feet, height 57 mm ... 67 mm

St, 1.5 mm, RAL 7021

Cable ducting 110 x 76 mm

Incl. GND/earthing

## SPECIFICAȚII

<b>Height:</b>	45mm
<b>Product Type:</b>	Cabinet/Rack Base
<b>Material:</b>	Oțel

Table 1/2

Număr de catalog	Width	Depth	Package Quantity	Color	Color Code	Finish
27230-072	553mm	800mm	1	Black Grey	RAL 7021	Vopsit Pulbere
27230-070	553mm	500mm	1	Black Grey	RAL 7021	Vopsit Pulbere
27230-080	1000mm	1000mm	1	Black Grey	RAL 7021	Vopsit Pulbere
27230-076	900mm	900mm	1	Black Grey	RAL 7021	Vopsit Pulbere
27230-071	553mm	600mm	1	Black Grey	RAL 7021	Vopsit Pulbere

Table 2/2

Număr de catalog	Type
27230-072	Base Plinth
27230-070	Base Plinth
27230-080	Base Plinth
27230-076	Base Plinth
27230-071	Base Plinth

## DETALII SUPLIMENTARE DESPRE PRODUS

Please order brush strip separately.

## AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe [www.nvent.com](http://www.nvent.com) și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

### North America

All locations

+1.763.422.2661

Chat with us:

[nvent.com/schroff](https://nvent.com/schroff)

### Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

[nvent.com/schroff](https://nvent.com/schroff)

### Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

[nvent.com/schroff](https://nvent.com/schroff)

### Middle East & India

Dubai, United Arab

Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

[nvent.com/schroff](https://nvent.com/schroff)



Portofoliul nostru puternic de mărci:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**