


Plug-In Unit Protection Panel

The panels protect the solder or the component side of a PCB. A coding with a separate coding strip is not possible.



CERTIFICATIONS



CARACTERISTICI

Keying/coding with separate keying/coding strip is not possible

Usable connectors in accordance with EN 60603 (DIN 41612): Construction type B, C, D, F, H, R

Stainless steel, 0.8 mm

SPECIFICAȚII

Product Type: Cover
Material: Stainless Steel


Table 1/1

Număr de catalog	Package Quantity	Works With
20809-371	1	Component Side
30809-571	1	Solder Side

DETALII SUPLIMENTARE DESPRE PRODUS

PCB is offset to the right by 1 HP.

DIAGRAMS



AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Portofoliul nostru puternic de mărci:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE