

PropacPRO Complete Desktop Case, Shielded



The nVent SCHROFF PropacPRO case provides electronics protection for 19" assemblies such as plug-in units and euroboards. The aluminum die cast frames and profile sidepanels guarantee a robust solution. The case includes EMC shielding as standard.

CERTIFICATIONS



CARACTERISTICI

Desktop case, pre-configured in accordance with IEC 60297-3-101 for 19" components

Shielded

Ventilation slots in base plate

Rear panel with vent slots

IP 20 in accordance with IEC 60529

Conforms with DIN EN 62368-1

SPECIFICAȚII

Static Load:	25kg
Product Type:	Case
Type:	Case for 19" Components
Product Family:	PropacPRO
EMC Shielding:	Yes

Table 1/3

Număr de catalog	Rack Height	Rack Width	Depth	Package Quantity	Usable Height	Usable Width
------------------	-------------	------------	-------	------------------	---------------	--------------

24576-122	6U	84HP	446mm	1	245.7mm	432mm
24576-105	3U	42HP	386mm	1	112.3mm	219mm
24576-102	3U	28HP	326mm	1	112.3mm	148mm
24576-110	3U	84HP	326mm	1	112.3mm	432mm
24576-111	3U	84HP	386mm	1	112.3mm	432mm
24576-121	6U	84HP	326mm	1	245.7mm	432mm
24576-104	3U	42HP	326mm	1	112.3mm	219mm
24576-106	3U	63HP	266mm	1	112.3mm	326mm
24576-109	3U	84HP	266mm	1	112.3mm	432mm
24576-112	3U	84HP	446mm	1	112.3mm	432mm
24576-113	3U	84HP	506mm	1	112.3mm	432mm
24576-103	3U	42HP	266mm	1	112.3mm	219mm
24576-107	3U	63HP	326mm	1	112.3mm	326mm
24576-101	3U	28HP	266mm	1	112.3mm	148mm
24576-108	3U	63HP	386mm	1	112.3mm	326mm

Table 2/3

Număr de catalog	Front Frame Construction	Cooling Option	Complies With	Finish	Height	Material
24576-122	Single Piece	No	IEC 60297-3-101	Passivated, Vopsit Pulbere	289mm	Aluminiu
24576-105	Single Piece	No	IEC 60297-3-101	Passivated, Vopsit Pulbere	155.5mm	Aluminiu
24576-102	Single Piece	No	IEC 60297-3-101	Passivated, Vopsit Pulbere	155.5mm	Aluminiu
24576-110	Single Piece	No	IEC 60297-3-101	Passivated, Vopsit Pulbere	155.5mm	Aluminiu
24576-111	Single Piece	No	IEC 60297-3-101	Passivated, Vopsit Pulbere	155.5mm	Aluminiu
24576-121	Single Piece	No	IEC 60297-3-101	Passivated, Vopsit Pulbere	289mm	Aluminiu
24576-104	Single Piece	No	IEC 60297-3-101	Passivated, Vopsit Pulbere	155.5mm	Aluminiu
24576-106	Single Piece	No	IEC 60297-3-101	Passivated, Vopsit Pulbere	155.5mm	Aluminiu
24576-109	Single Piece	No	IEC 60297-3-101	Passivated, Vopsit Pulbere	155.5mm	Aluminiu
24576-112	Single Piece	No	IEC 60297-3-101	Passivated, Vopsit Pulbere	155.5mm	Aluminiu

Număr de catalog	Front Frame Construction	Cooling Option	Complies With	Finish	Height	Material
24576-113	Single Piece	No	IEC 60297-3-101	Passivated, Vopsit Pulbere	155.5mm	Aluminiu
24576-103	Single Piece	No	IEC 60297-3-101	Passivated, Vopsit Pulbere	155.5mm	Aluminiu
24576-107	Single Piece	No	IEC 60297-3-101	Passivated, Vopsit Pulbere	155.5mm	Aluminiu
24576-101	Single Piece	No	IEC 60297-3-101	Passivated, Vopsit Pulbere	155.5mm	Aluminiu
24576-108	Single Piece	No	IEC 60297-3-101	Passivated, Vopsit Pulbere	155.5mm	Aluminiu

Table 3/3

Număr de catalog	Protection Rating	Width
24576-122	IP20	470.3mm
24576-105	IP20	257mm
24576-102	IP20	185.9mm
24576-110	IP20	470.3mm
24576-111	IP20	470.3mm
24576-121	IP20	470.3mm
24576-104	IP20	257mm
24576-106	IP20	363.7mm
24576-109	IP20	470.3mm
24576-112	IP20	470.3mm
24576-113	IP20	470.3mm
24576-103	IP20	257mm
24576-107	IP20	363.7mm
24576-101	IP20	185.9mm
24576-108	IP20	363.7mm

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

North America

All locations

+1.763.422.2661

Chat with us:

nvent.com/schroff

Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

nvent.com/schroff

Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

nvent.com/schroff

Middle East & India

Dubai, United Arab

Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

nvent.com/schroff



Portofoliul nostru puternic de mărci:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE