

# Socket Strip, UTE, With Wieland® Input



Modular, compact PDU with many function elements. Using a 1 U by 1 U aluminum chassis the PDU can easily be integrated in a rack. The Wieland connector allows easy combination with different power input cords.

## CERTIFICATIONS



## CARACTERISTICI

Input via Wieland® GST 18 plug

Socket strips can be rotated through all four directions (in 90° increments) during fitting

Output via UTE sockets

Horizontal or vertical mounting

Installation height 1 U

In accordance with NFC 61-303

## SPECIFICAȚII

- Length:** 438.5mm  
**Material:** Aluminiu; Polyamide  
**Product Type:** Socket Strip

Table 1/2

Număr de catalog	Socket Type	Socket Quantity	Switched Outlets	Voltage AC	Function	Package Quantity
60110-357	UTE	6	No	230V	Overcurrent Protection	1

Număr de catalog	Socket Type	Socket Quantity	Switched Outlets	Voltage AC	Function	Package Quantity
60110-356	UTE	6	No	230V	Overcurrent Protection	1
60110-346	UTE	8	No	230V		1
60110-355	UTE	6	No	230V	Overcurrent Protection	1
60110-348	UTE	8	No	230V		1
60110-347	UTE	8	No	230V		1

Table 2/2

Număr de catalog	Color	Depth	Finish
60110-357	Red	44mm	Anodized
60110-356	Black	44mm	Anodized
60110-346	White	44mm	Anodized
60110-355	White	44mm	Anodized
60110-348	Red	44mm	Anodized
60110-347	Black	44mm	Anodized

## DETALII SUPLIMENTARE DESPRE PRODUS

Please order mounting bracket for vertical mounting separately.

## AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe [www.nvent.com](http://www.nvent.com) și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

### North America

All locations

+1.763.422.2661

Chat with us:

[nvent.com/schroff](https://nvent.com/schroff)

### Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

[nvent.com/schroff](https://nvent.com/schroff)

### Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

[nvent.com/schroff](https://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

[nvent.com/schroff](https://nvent.com/schroff)



Portofoliul nostru puternic de mărci:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**