

Varistar CP Base/Plinth Side

Sides trim to mount to Varistar CP base/plinth



CARACTERISTICI

Base/plinth sides, plain

SPECIFICAȚII

Product Type: Cabinet/Rack Base

Material: Oțel

Table 1/2

Număr de catalog	Height	Depth	Package Quantity	Color	Color Code	Finish
24630-077	100mm	600mm	1	Black Grey	RAL 7021	Vopsit Pulbere
24630-083	100mm	300mm	1	Black Grey	RAL 7021	Vopsit Pulbere
24630-043	200mm	1200mm	1	Black Grey	RAL 7021	Vopsit Pulbere
24630-078	100mm	800mm	1	Black Grey	RAL 7021	Vopsit Pulbere
24630-040	100mm	1200mm	1	Black Grey	RAL 7021	Vopsit Pulbere
24630-080	200mm	600mm	1	Black Grey	RAL 7021	Vopsit Pulbere
24630-042	200mm	1100mm	1	Black Grey	RAL 7021	Vopsit Pulbere
24630-081	200mm	800mm	1	Black Grey	RAL 7021	Vopsit Pulbere
24630-038	100mm	1000mm	1	Black Grey	RAL 7021	Vopsit Pulbere
24630-079	100mm	900mm	1	Black Grey	RAL 7021	Vopsit Pulbere
24630-084	200mm	300mm	1	Black Grey	RAL 7021	Vopsit Pulbere
24630-039	100mm	1100mm	1	Black Grey	RAL 7021	Vopsit Pulbere
24630-082	200mm	900mm	1	Black Grey	RAL 7021	Vopsit Pulbere

Număr de catalog	Height	Depth	Package Quantity	Color	Color Code	Finish
24630-041	200mm	1000mm	1	Black Grey	RAL 7021	Vopsit Pulbere

Table 2/2

Număr de catalog	Type	Package Unit
24630-077	Plinth Side	Pair
24630-083	Plinth Side	
24630-043	Plinth Side	Pair
24630-078	Plinth Side	Pair
24630-040	Plinth Side	Pair
24630-080	Plinth Side	Pair
24630-042	Plinth Side	Pair
24630-081	Plinth Side	Pair
24630-038	Plinth Side	Pair
24630-079	Plinth Side	Pair
24630-084	Plinth Side	
24630-039	Plinth Side	Pair
24630-082	Plinth Side	Pair
24630-041	Plinth Side	Pair

DETALII SUPLIMENTARE DESPRE PRODUS

Please order base/plinth for front/rear separately.

Cannot be used in conjunction with castors

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

North America

All locations

+1.763.422.2661

Chat with us:

nvent.com/schroff

Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

nvent.com/schroff

Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

nvent.com/schroff



Portofoliul nostru puternic de mărci:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE