

Varistar CP Server Cabinet



Welded steel frame for high static load requirements.
Prepared for 19" integration of IT assets.

CARACTERISTICI

Preconfigured, ready to use cabinet

Static load-carrying capacity up to 1600 kg, dynamic 1000 kg

Ingress protection class IP 20

Installation of different IT equipment possible

Integrated air panels for front to back cooling

Can be easily integrated into aisle containment system

SPECIFICAȚII

Static Load:	1600kg
Product Type:	Rack
Cladding Color Code:	RAL 7021
Frame Material:	Oțel

Table 1/2

Număr de catalog	Rack Height	Height	Cladding Material	Width	Cladding Color	Depth
10630-019	47U	2200mm	Oțel	600mm	Black Grey	1200mm
10630-017	42U	2000mm	Oțel	600mm	Black Grey	1200mm
10630-026	47U	2200mm	Oțel	800mm	Black Grey	1200mm

Număr de catalog	Rack Height	Height	Cladding Material	Width	Cladding Color	Depth
10630-023	42U	2000mm	Oțel	600mm	Black Grey	1200mm
10630-018	42U	2000mm	Oțel	800mm	Black Grey	1200mm
10630-020	47U	2200mm	Oțel	800mm	Black Grey	1200mm
10630-024	42U	2000mm	Oțel	800mm	Black Grey	1200mm
10630-025	47U	2200mm	Oțel	600mm	Black Grey	1200mm

Table 2/2

Număr de catalog	Type	Package Quantity	Dynamic Load	Finish	Material
10630-019	Standard	1	1000kgf	Vopsit Pulbere	Oțel
10630-017	Standard	1	1000kgf	Vopsit Pulbere	Oțel
10630-026	Side-by-Side	1	1000kgf	Vopsit Pulbere	Oțel
10630-023	Side-by-Side	1	1000kgf	Vopsit Pulbere	Oțel
10630-018	Standard	1	1000kgf	Vopsit Pulbere	Oțel
10630-020	Standard	1	1000kgf	Vopsit Pulbere	Oțel
10630-024	Side-by-Side	1	1000kgf	Vopsit Pulbere	Oțel
10630-025	Side-by-Side	1	1000kgf	Vopsit Pulbere	Oțel

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Portofoliul nostru puternic de mărci:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE