

VMEbus J2 Backplane

The nVent SCHROFF VMEbus Backplanes have outstanding high-frequency noise suppression and very high MTBF values due to ceramic capacitors and SMD fabrication technology.



CERTIFICATIONS



CARACTERISTICI

In accordance with ANSI/VITA 1-1994 VME64 standard

3 U with J2 plane

Connection or isolation between the digital GND and chassis GND can be changed via screw

Termination passive

Supply voltages can be provided via powerbugs (ring tag M4) or FASTONs

Multiple backplanes can be placed side by side without loss of slot space

SPECIFICAȚII

Table 1/2

Număr de catalog	Product Type	Number of Slots	Rack Height	Backplane Type	System Slot	Slot Width
23001-051	Backplane	21	3U	VMEbus, J2	Slot 1 Left	4HP
23001-046	Backplane	16	3U	VMEbus, J2	Slot 1 Left	4HP
23001-040	Backplane	10	3U	VMEbus, J2	Slot 1 Left	4HP
23001-036	Backplane	6	3U	VMEbus, J2	Slot 1 Left	4HP
23001-035	Backplane	5	3U	VMEbus, J2	Slot 1 Left	4HP

Număr de catalog	Product Type	Number of Slots	Rack Height	Backplane Type	System Slot	Slot Width
23001-034	Backplane	4	3U	VMEbus, J2	Slot 1 Left	4HP
23001-033	Backplane	3	3U	VMEbus, J2	Slot 1 Left	4HP
23001-032	Backplane	2	3U	VMEbus, J2	Slot 1 Left	4HP

Table 2/2

Număr de catalog	Connector Type	Power Connector Type	Height	Width	Package Quantity
23001-051	DIN 41612, C96	Power Bugs for M4 Cable Lugs	128.5mm	425.3mm	1
23001-046	DIN 41612, C96	Power Bugs for M4 Cable Lugs	128.5mm	321.3mm	1
23001-040	DIN 41612, C96	Power Bugs for M4 Cable Lugs	128.5mm	199.2mm	1
23001-036	DIN 41612, C96	Power Bugs for M4 Cable Lugs	128.5mm	120.5mm	1
23001-035	DIN 41612, C96	Power Bugs for M4 Cable Lugs	128.5mm	100.2mm	1
23001-034	DIN 41612, C96	Power Bugs for M4 Cable Lugs	128.5mm	79.8mm	1
23001-033	DIN 41612, C96	Power Bugs for M4 Cable Lugs	128.5mm	59.7mm	1
23001-032	DIN 41612, C96	Power Bugs for M4 Cable Lugs	128.5mm	40.4mm	1

DETALII SUPLIMENTARE DESPRE PRODUS

Other configurations available on request.

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Portofoliul nostru puternic de mărci:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE