

Syspend 180-Max flänskoppling



Syspend 180-Max Flange Coupling attaches a tube to the enclosure, enabling 300-degree enclosure rotation and can be locked into a given position. The flange coupling has a safety stop and maintenance-free bearings.

DESIGN

Coupling can rotate 300 degrees with stop

Gasket, set screws, and mounting hardware are included

Assembled Syspend 180 HMI Arm System has a max weight load of 180 lb. (81.6 kg)

SPECIFIKATIONER

Material: Aluminium

Yta: Pulverlackerad

Table 1/1

Katalognummer	Höjd	Bredd	Djup	Färg	Färgkod
S1MFCG	101mm	125mm	100mm	Ljusgrå	RAL 7035
S1MFC	174mm	133mm	125mm	Jet Black	RAL 9005

VARNING

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial. Bruksanvisningar är tillgängliga på www.nvent.com och från din nVent kundtjänstrepresentant. Felaktig installation, missbruk, felapplicering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister, egendomsskador, allvarliga kroppsskador och dödsfall och/eller ogiltigförklara din garanti.



Vårt starka utbud av varumärken:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTe