


Comptec jord-/jordningssats



Skyddande jord-/jordanslutningar i enlighet med: DIN EN 50178, VDE 0160 DIN EN 62368-1, VDE 0805 DIN EN 61010?1, VDE 0411 DEL 1 DIN EN 61010?1A2, VDE 0411 DEL 1/A1.

CERTIFIERINGAR



DESIGN

Skyddande jord-/jordanslutningar i enlighet med: DIN EN 50178/VDE 0160 DIN EN 62368-1/VDE 0805 DIN EN 61010?1 /VDE 0411 DEL 1 DIN EN 61010?1A2 /VDE 0411 DEL 1/A1

VDE-testad

SPECIFIKATIONER

Produktfamilj: Comptec
Typ: Jordningssats
Produkttyp: Jordningssats

Table 1/1

Katalognummer	Antal i förpackningen	Fungerar med
21100-490	1	Lådor, Stålkåpa
21100-448	1	Lådor, Stålkåpa
21100-347	1	Lådor, Aluminiumhölje

VARNING

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial. Bruksanvisningar är tillgängliga på www.nvent.com och från din nVent kundtjänstrepresentant. Felaktig installation, missbruk, felapplicering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister, egendomsskador, allvarliga kroppsskador och dödsfall och/eller ogiltigförklara din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vårt starka utbud av varumärken:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE