

Enlogic Basic PDU

Data Solutions



The Basic PDU is a cost-effective, reliable power distribution solution. Premium hydraulic-magnetic circuit breakers operate consistently in high-temperature environments. The Basic PDU offers advanced features, such as color-coded locking IEC outlets, a slim chassis design, and toolless mounting backed by a 5-year hassle-free warranty.

功能

Black Powder Coated Chassis

IEC 62368 listed. RoHS, and REACH compliant. See drawing for additional information.

技术参数

Table 1/6

物料号	产品系列	类型	产品类型	插座类型	插座数量	颜色
EB0860	Enlogic	基本型 PDU	插排	(24) C13/C15, (24) C13/C15/C19/C 21	48	黑色
EB09JA	Enlogic	基本型 PDU	插排	(18) C13/C15, (18) C13/C15/C19/C 21	36	黑色
EB0360	Enlogic	基本型 PDU	插排	(16) C13/C15	20	黑色

Table 2/6

物料号	开关插座	电缆长度	断路器	额定功率	断路器数量	中断额定值
EB0860	否	3000mm	20 A, 1 极, Hy-MagA	17.3 kVA 北美, 22.1 kVA 国际	6	

物料号	开关插座	电缆长度	断路器	额定功率	断路器数量	中断额定值
EB09JA	否	1800mm	20 A, 1 极, Hy-MagA	34.6 kVA 北美, 43.5 kVA 国际	12	
EB0360	否	3000mm	16 A, 1 极, Hy-Mag	7.4 kVA	2	5kAIC

Table 3/6						
物料号	标称输出功率	标称电压	输出电压数	相数	包含通/断开关	电流（降额电流）
EB0860	230VAC	415V			否	30 A (24 A) 北美, 32 A 国际
EB09JA	230VAC	415V	36		否	60 A (48 A) 北美, 63 A 国际
EB0360	230VAC	230V	20	1	否	32 A

Table 4/6						
物料号	输出电压	机架单元	插头类型	计量类型	可拆卸输入电缆	材料
EB0860	208 – 230VAC	0U	IEC 60309 530P6/532P6	无	否	钢
EB09JA	208 – 230VAC	0U	IEC 60309 560P6/563P6	无	否	钢
EB0360	230VAC	0U	IEC 60309 332P6 (IP44)	无	否	钢

Table 5/6						
物料号	完成	高度	宽度	深度	重量	包装数量
EB0860	粉末涂层	1490mm	56mm	55mm		1
EB09JA	粉末涂层	965mm	114mm	75mm		1
EB0360	粉末涂层	817mm	52mm	53mm	3.6kg	1

Table 6/6	
物料号	输入电缆长度
EB0860	3m
EB09JA	1.8m
EB0360	3m

其他产品详情

Warranty : nVent Enlogic branded equipment provided shall be free from manufacturing defects for a period of five (5) years from the invoice date to the original purchaser.

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE