



Part	Material	Size 1	Size 1 mm	Size 2	Size 2 mm
CAPCT1L1E	PC	#4	5.89mm	#8	3.71mm
CASST1G	SS	#6	4.11mm	#6	4.11mm
CAPCT1G1G	PT	#6	4.11mm	#6	4.11mm
CAPCP2G1G	PC	2/0	10.62mm	#6	4.11mm
CAPCT1V1G	PC	#2	7.42mm	#6	4.11mm
CAPCT1L1H	PC	#4	5.89mm	#6	4.67mm
CAPCP2C1H	PC	1/0	9.47mm	#6	4.67mm
CAPCT1V1H	PC	#2	7.42mm	#6	4.67mm
CAPCT1H1H	PC	#6	4.67mm	#6	4.67mm
CASST1H	SS	#6	4.67mm	#6	4.67mm
CASST1K	SS	#4	5.18mm	#4	5.18mm
CASST1L	SS	#4	5.89mm	#4	5.89mm
CATAN2C1L	TA	1/0	9.47mm	#4	5.89mm
CATAN1V1L	TA	#2	7.42mm	#4	5.89mm

Table 2/2

Part	Material	Size 1	Size 1 mm	Size 2	Size 2 mm
CAPCT1L1LM	PC	#4	5.89mm	#4	5.89mm
CAPCP2C1L	PC	1/0	9.47mm	#4	5.89mm
CAPCT1L1L	PC	#4	5.89mm	#4	5.89mm
CATAN2G1L	TA	2/0	10.62mm	#4	5.89mm
CASST1V	SS	#2	7.42mm	#2	7.42mm
CATAN1V1V	TA	#2	7.42mm	#2	7.42mm
CATAN1Y1V	TA	#1	8.43mm	#2	7.42mm
CAPCP2C1V	PC	1/0	9.47mm	#2	7.42mm
CATAN2C1V	TA	1/0	9.47mm	#2	7.42mm
CAPCP1V1V	PC	#2	7.42mm	#2	7.42mm
CATAN2G1V	TA	2/0	10.62mm	#2	7.42mm
CAPCN2G1V	PC	2/0	10.62mm	#2	7.42mm
CASST1Y	SS	#1	8.43mm	#1	8.43mm
CATAN2C1Y	TA	1/0	9.47mm	#1	8.43mm
CATAN2C1YM	TA	1/0	9.47mm	#1	8.43mm
CASSP2C	SS	1/0	9.47mm	1/0	9.47mm
CATAN2C2C	TA	1/0	9.47mm	1/0	9.47mm

