

全高摇架，ESFC



A swing frame for 19" equipment that provides additional mounting space for such equipment, as well as rear access to the fitted components and equipment once opened.

功能

Description: Full height swing frame for 19" components allowing left and right hand opening. Can be used in steel, combinable and compact enclosures. Hinges designed to give extra build-in depth. Adjustable top hinge for square mounting of the swing frame. Rigid W-shaped frame profile for heavy equipment. Zinc plated 19" vertical profiles for direct earthing of the mounted components. Standard equipped with 130° hinges. Can also be mounted on the side of 600 mm deep floor standing enclosures. For steel, combinable enclosures use transversal support bars ESFB in combination with VBD if required. Adjustable in depth by steps of 12.5 mm.

Maximum load: 1800N, supplied with a self positioning device.

Lock: Two 3 mm double-bit locks.

Material: 19" vertical profiles 2 mm zinc plated steel. Frame: vertical profiles 2 mm and horizontal profiles 3 mm.

Pack quantity: 1 swing frame with hinges.

Mounting requirements: ESFC for 600 mm, 800 mm, 1000 mm, 1200 mm wide steel, combinable enclosures. Add ESFB for mounting in a steel, combinable enclosure.

技术参数

厚度: 2mm

材料: 低碳钢

完成: 镀锌

Table 1/1

| 物料号 | 订货号 | 高度 | 宽度 | 深度 | 机架单元 | 外壳材料 |
|---------|---------|--------|-------|------|------|------|
| ESFC316 | ESFC316 | 1600mm | 499mm | 80mm | 31U | 低碳钢 |
| ESFC456 | ESFC456 | 2200mm | 499mm | 80mm | 45U | 低碳钢 |
| ESFC406 | ESFC406 | 2000mm | 499mm | 80mm | 40U | 低碳钢 |
| ESFC276 | ESFC276 | 1400mm | 499mm | 80mm | 27U | 低碳钢 |
| ESFC366 | ESFC366 | 1800mm | 499mm | 80mm | 36U | 低碳钢 |

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE