

eHandle



The security access control eHandle is an intelligent electromechanical locking system for server and networking cabinets. The eHandle seamlessly integrates with the network controller and RackPower iPDUs to serve as a hub for access control and environmental monitoring.

功能

用于 nVent SCHROFF RackPower iPDU 的安全访问控制把手

单一或双重身份验证

三重嵌入式感应读卡器，支持 MIFARE Classic 4k - UID, MIFARE Plus 2k - UID, MIFARE DESFire 4k - UID, HIS iClass - UID, HID 125 kHz prox - CSN 和 EM125 kHz Prox - CSN

远程锁定/解锁和远程监控

本地锁定状态指示器，带多色 LED 指示器

双面可见 LED 警示灯，指示电源状况, 机架环境, 或安全警报状态

用户可定制按键锁，实现手动超控

嵌入式湿度传感器和附加环境传感器端口

本地数据存储，可保存 200 个用户凭据和 500 个本地事件

可定制警报, LED 状态, 和访问配置设置

技术参数

Table 1/1

物料号	产品类型	搭配	包装数量	插头类型	可拆卸输入电缆
EA9500	手柄	RackPower	1	RJ45	否
EA9502	手柄	RackPower	1	RJ45	否

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent

的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations

+1.763.422.2661

Chat with us:

nvent.com/schroff

Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

nvent.com/schroff

Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

nvent.com/schroff

Middle East & India

Dubai, United Arab

Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

nvent.com/schroff



我们强大的品牌组合:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE