

插排, 英标

模块化、紧凑型 PDU，支持多种功能。PDU 采用 1 U x 1 U 铝机箱，可轻松集成在带英标插座的机架中。



认证



功能

水平或垂直安装

安装时，插排可以向四个方向旋转（90°增量）

符合 BS 1363

安装高度 1 U

提供电缆 2 米，带英国标准插头（集成熔断器）

插座条，带英国标准插座

230 V, 13 A

技术参数

材料: 铝; 聚酰胺

颜色: 灰色

产品类型: 插排

Table 1/2

物料号	插座类型	插座数量	开关插座	交流电压	包装数量	深度
60110-245	英标	6	是	230V	1	44mm
60110-243	英标	7	否	230V	1	44mm
60110-244	英标	10	否	230V	1	44mm

Table 2/2

物料号	完成	长度
60110-245	阳极氧化	438.5mm
60110-243	阳极氧化	438.5mm
60110-244	阳极氧化	947.5mm

其他产品详情

请单独订购垂直安装支架。

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE