

插排, UTE

模块化、紧凑型 PDU，支持多种功能。PDU 采用 1 U x 1 U 铝机箱，可轻松集成在带 UTE 插座的机架中。



认证



功能

符合 NFC 61-303 标准

带 UTE 插座的插座条

安装高度 1 U

水平或垂直安装

连接电缆 2 米, 带 SCHUKO/UTE 插头

安装时, 插排可以向四个方向旋转 (90°增量)

230 V, 16 A

技术参数

材料: 铝; 聚酰胺

颜色: 灰色

产品类型: 插排

Table 1/2

物料号	插座类型	插座数量	开关插座	交流电压	功能	包装数量
60110-226	UTE	12	是	230V		1
60110-222	UTE	12	否	230V		1
60110-221	UTE	9	否	230V		1
60110-267	UTE	6	否	230V	瞬态保护, 电源抑制过滤器	1
60110-223	UTE	15	否	230V		1
60110-224	UTE	19	否	230V		1
60110-225	UTE	8	是	230V		1
60110-231	UTE	6	否	230V	故障电流保护, 过流保护	1
60110-227	UTE	8	否	230V	瞬态保护	1
60110-228	UTE	6	否	230V	过流保护	1
60110-220	UTE	4	否	230V		1
60110-230	UTE	6	否	230V	故障电流保护	1
60110-229	UTE	7	否	230V	电源抑制过滤器	1

Table 2/2

物料号	深度	完成	长度
60110-226	44mm	阳极氧化	947.5mm
60110-222	44mm	阳极氧化	947.5mm
60110-221	44mm	阳极氧化	438.5mm
60110-267	44mm	阳极氧化	438.5mm
60110-223	44mm	阳极氧化	1202mm
60110-224	44mm	阳极氧化	1753mm
60110-225	44mm	阳极氧化	438.5mm
60110-231	88mm	阳极氧化	438.5mm
60110-227	44mm	阳极氧化	438.5mm
60110-228	75mm	阳极氧化	438.5mm
60110-220	44mm	阳极氧化	210mm
60110-230	88mm	阳极氧化	438.5mm

物料号	深度	完成	长度
60110-229	44mm	阳极氧化	438.5mm

其他产品详情

请单独订购垂直安装支架。

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE