

# PDU, 0U, 60A(48A)NA/63A Int, 380-415V, 3P Wye, 12 CB (18)C13 (18)4-in-1

## Data Solutions

### 物料号

## EB09JA

The Basic PDU is a cost-effective, reliable power distribution solution. Premium hydraulic-magnetic circuit breakers operate consistently in high-temperature environments. The Basic PDU offers advanced features, such as color-coded locking IEC outlets, a slim chassis design, and toolless mounting backed by a 5-year hassle-free warranty.

### 功能

Black Powder Coated Chassis

IEC 62368 listed. RoHS, and REACH compliant. See drawing for additional information.

### 产品属性

产品系列: Enlogic

类型: 基本型 PDU

产品类型: 插排

插座类型: (18) C13/C15; (18) C13/C15/C19/C21

插座数量: 36

颜色: 黑色

开关插座: 否

电缆长度: 1800mm

断路器: 20 A, 1 极, Hy-MagA

额定功率: 34.6 kVA 北美; 43.5 kVA 国际

断路器数量: 12

标称输出功率: 230VAC

标称电压: 415V

输出电压数: 36

包含通/断开关: 否

电流 (降额电流) : 60 A (48 A) 北美; 63 A 国际

输出电压: 208 – 230VAC

机架单元: 0U

插头类型: IEC 60309 560P6/563P6

计量类型: 无

可拆卸输入电缆: 否

材料: 钢

完成: 粉末涂层

高度: 965mm

宽度: 114mm

深度: 75mm

包装数量: 1

输入电缆长度: 1.8m

## 其他产品详情

---

Warranty : nVent Enlogic branded equipment provided shall be free from manufacturing defects for a period of five (5) years from the invoice date to the original purchaser.

## 警告

---

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 [www.nvent.com](http://www.nvent.com) 获取说明书, 或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告, 可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。



我们强大的品牌组合:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**