

# 插排, IEC C19

模块化、紧凑型 PDU，支持多种功能。PDU 采用 1 U x 1 U 铝机箱，可轻松集成在带 IEC C19 插座的机架中。



## 认证



## 功能

带有 IEC C19 插座的插排

安装时，插排可以向四个方向旋转（90°增量）

连接电缆 2 米, 带符合 IEC 60309 标准的连接器

安装高度 1 U

安装高度 1 U

## 技术参数

材料: 铝; 聚酰胺

颜色: 灰色

产品类型: 插排

Table 1/2

物料号	插座类型	插座数量	开关插座	交流电压	包装数量	深度
60110-280	IEC C19	8	否	230V	1	44mm

物料号	插座类型	插座数量	开关插座	交流电压	包装数量	深度
60110-282	IEC C19	12	否	230V	1	44mm
60110-281	IEC C19	12	否	230V	1	44mm

Table 2/2

物料号	完成	高度	长度
60110-280	阳极氧化	44mm	438.5mm
60110-282	阳极氧化	44mm	947.5mm
60110-281	阳极氧化	44mm	947.5mm

## 其他产品详情

请单独订购垂直安装支架。

## 警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 [www.nvent.com](http://www.nvent.com) 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



我们强大的品牌组合:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**