


Joint Bond T6 Complete Welder Pair, Signal, 1" Tab Bond Terminal Style, 5/16" Bondstrand

Data Solutions

CATALOG NUMBER

SBTBT6B



FEATURES

Complete welder assembly provides a convenient means of attaching jumper bonds to the head of the rail, across the joint

Connection is made within the confines of the splice bar

Includes mold cleaner

PRODUCT ATTRIBUTES

Material: Steel; Graphite; Thermoplastic

Rail Type: 85 lb to 141 lb T-Rail Sections

Bond Terminal Style: 1" Tab

Conductor Size: 5/16" Bondstrand

Conductor Outer Diameter, Nominal: 0.79mm

Bond Length: 177.8mm

Welder Style: T6

Mold Only: No

Replacement Mold: SBS898

Welding Material: SB32 x 2, Sold Separately

Frame: SBS5838F, Sold Separately

Bond Clip: SBS119 x 2, Sold Separately

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE