

# 19" Mounting Bracket

Easy mounting for connection system for networks which are reliable, gas-tight connection between the contact and conductor.



## CERTIFICATIONS



## VLASTNOSTI

Mounting height 1 U

For the assembly of cable channels and system rails (Z.w.LSA+ or Infra+)

## SPECIFIKACE

**Product Type:** Bracket

**Materiál:** Ocel

Table 1/1

Katalogové číslo	Hloubka	Množství v balení	Povrchová úprava	Typ	Works With
30118-802	70mm	1	Strukturovaný Práškový	Mounting Bracket	LSA+ Guide Rails
30118-803	170mm	1	Strukturovaný Práškový	Mounting Bracket	LSA+ Guide Rails

## DALŠÍ PODROBNOSTI O PRODUKTU

Please order 19" assembly kit separately.

## UPOZORNĚNÍ

---

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na [www.nvent.com](http://www.nvent.com) a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Naše portfolio silných značek:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**