

LHX+ Control Unit



The Control Unit enriches the LHX+. It connects to the LHX+ sensors and the motorized coolant valve 23130-607. This enables the cooler to control the coolant air flow based on a chilled (supply) air temperature setpoint. It provides advanced remote monitoring functionality and various setup features.

VLASTNOSTI

Coolant flow control based on chilled (supply) air temperature setpoint. More control features with water control package

Separate, compact 19" control unit without loose wires in upper cabinet section

Clearly marked plug & play sensor connections

SPECIFIKACE

| | |
|----------------------|--------------|
| Rack Height: | 2U |
| Product Type: | Control Unit |
| Materiál: | Ocel |

Table 1/2

| Katalogové číslo | Výška | Hloubka | Works With | Množství v balení | Barva | Kód barvy |
|------------------|-------|---------|--------------------------|-------------------|------------|-----------|
| 23130-668 | 88mm | 220mm | Varistar, Varistar CP | 1 | Black Grey | RAL 7021 |
| 23130-664 | 88mm | 220mm | Varistar, Varistar CP | 1 | Black Grey | RAL 7021 |

Table 2/2

| Katalogové číslo | Povrchová úprava | Vstupní napětí AC | Šířka |
|------------------|----------------------|-------------------|---------|
| 23130-668 | Aluminum-Zinc Plated | 230V | 439.5mm |
| 23130-664 | Aluminum-Zinc Plated | 100 – 260V | 439.5mm |

DALŠÍ PODROBNOSTI O PRODUKTU

Optional external display.

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Naše portfolio silných značek:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE