

Socket Strip, SCHUKO

Data Solutions



Modular, compact PDU with many function elements. Using a 1 U by 1 U aluminum chassis the PDU can easily be integrated in a rack with Schuko outlets.

CERTIFICERINGER



FUNKTIONER

230 V, 16 A

Horizontal or vertical mounting

Connecting cable 2 m with SCHUKO/UTE plug

In accordance with DIN 57620, VDE 0620

Installation height 1 U

Socket strips with SCHUKO sockets

Socket strips can be rotated through all four directions (in 90° increments) during installation

SPECIFIKATIONER

Materiale: Aluminium; Polyamide

Farve: Grey

Product Type: Socket Strip

Table 1/2

Katalognummer	Stiktype	Socket Quantity	Switched Outlets	Spænding AC	Function	Pakke mængde
60110-207	SCHUKO	12	Yes	230V		1
60110-202	SCHUKO	9	No	230V		1
60110-266	SCHUKO	6	No	230V	Transient Protection, Mains Suppression Filter	1
60110-203	SCHUKO	12	No	230V		1
60110-204	SCHUKO	15	No	230V		1
60110-205	SCHUKO	19	No	230V		1
60110-217	SCHUKO	6	No	230V	Fault Current Protection, Overcurrent Protection	1
60110-201	SCHUKO	4	No	230V		1
60110-206	SCHUKO	8	Yes	230V		1
60110-208	SCHUKO	15	Yes	230V		1
60110-216	SCHUKO	6	No	230V	Fault Current Protection	1
60110-209	SCHUKO	19	Yes	230V		1
60110-210	SCHUKO	8	No	230V	Transient Protection	1
60110-211	SCHUKO	9	No	230V	Transient Protection	1
60110-214	SCHUKO	7	No	230V	Mains Suppression Filter	1
60110-200	SCHUKO	3	No	230V		1
60110-212	SCHUKO	6	No	230V	Overcurrent Protection	1

Table 2/2

Katalognummer	Dybde	Finish	Length
60110-207	44mm	Anodized	947.5mm
60110-202	44mm	Anodized	438.5mm
60110-266	44mm	Anodized	438.5mm
60110-203	44mm	Anodized	947.5mm
60110-204	44mm	Anodized	1202mm

Katalognummer	Dybde	Finish	Length
60110-205	44mm	Anodized	1753mm
60110-217	88mm	Anodized	438.5mm
60110-201	44mm	Anodized	210mm
60110-206	44mm	Anodized	438.5mm
60110-208	44mm	Anodized	1202mm
60110-216	88mm	Anodized	438.5mm
60110-209	44mm	Anodized	1753mm
60110-210	44mm	Anodized	438.5mm
60110-211	44mm	Anodized	947.5mm
60110-214	44mm	Anodized	438.5mm
60110-200	44mm	Anodized	184mm
60110-212	75mm	Anodized	438.5mm

YDERLIGERE PRODUKTOPLYSNINGER

Please order mounting bracket for vertical mounting separately.

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE